

# DPGL Series Modulated Green Laser Module

Part No: DPGL-01S-TTL



## Product Features

- High Stability and low noise
- Collimated beam
- Reverse Polarity Protection
- Custom Options Available

## Application

- Measurement
- Bioanalytical
- Automation
- Alignment

## Mechanical Drawing



### Operational Hazard-Semiconductor Laser Diode Module:

When in use, do not look directly into the laser emitting aperture. Direct viewing of laser diode emission at close range may cause eye damage.

**Limited Warranty:** One year. No warranty coverage for disassembly, modifications or damage due to abuse or misapplication.

## Specification

OPTICAL	
Wavelength	532 nm
Optical Output Power	<1 mW
Stability	<1%
Spatial Mode	TEM <sub>00</sub>
Laser Class	Class II
Laser Operation	Continuous
Divergence at the collimation	< 1 milliradian
Beam Diameter <sub>1/e<sup>2</sup></sub>	<1.2mm
Beam Shape	Circular(1:1.1)
ELECTRICAL	
Operating Voltage <sup>1</sup>	3 VDC
Operating Current	<200 mA
Modulation	0 Hz to 3 kHz
TTL Input	Low (0~0.8 V), High (1~3.3V)
Electrical Connections	+Red, -Black, TTL(White)
MECHANICAL	
Dimension	15mm(D)x 69mm (L)
Cable	200mm
Operating Temperature	+10°C to +30°C
Storage Temperature	-40°C to +80°C
Heat Sink Requirements <sup>2</sup>	Recommended for extended use

### Notes

1. Preferably operate at 3V, higher voltage will result in excessive heat.

2. Heat Sink: The DPGL Series Green Laser Module is designed to operate without heat sink. Do not restrict air circulation around the device; an additional heat sink can be used to maximize the performance and life time of the laser.

**Caution:** The case is internally connected to the circuit; damaging to the anodized surface may result in failure of the laser module.



Complies with CDRH 21CFR 1040.10

## World Star Tech.

321 Lesmill Rd. Toronto, Ont. M3B 2V1 Canada  
Tel: (416) 363-3332 Fax: (416) 363-3112 www.worldstartech.com


Rev. B Oct.2004

# DPGL Series Modulated Green Laser Module

*Part No: DPGL-01S-TTL*

## TTL Modulation

The DPGL series Modulated Green laser module is TTL modulatable between 0 and the full power by applying an external TTL input signal (e.g. from function generator) using third white wire. When the TTL input is Low the laser power is completely off. When the TTL input is high the laser output is at Full Power. The TTL signal can be any on-off time combination.



## Continuously Operation

The UT series laser module can be operated continuously by applying a high signal to the TTL input which can be done by connecting the white wire and red wire together.

